

We're delighted that you've chosen to use our coating service! This quick guide provides you with all the information you need to get started straight away. You can find further information on our website and in the [Forms | Shape Line](#) download section.


## Follow these 4 simple steps to offer shape·line:

### 1. Check the glass specifications: Is shape·line possible?

Lens specification requirements		
Bevel type	Full-rim glasses (bevel)	<input checked="" type="checkbox"/>
Lens material	Plastic lenses, index 1.5, 1.6, 1.67 or 1.74	<input checked="" type="checkbox"/>
Coatings	The lenses have an AR coating (preferably hydrophobic)	<input checked="" type="checkbox"/>
Photochrom	The lenses are not photochromic *	<input checked="" type="checkbox"/>

\*Some lens types can be coated at your own risk; please enquire

### 2. Choose a colour: Choose from 26 shape·line colours



### 3. Edging: Three edging guidelines for the best shape·line result

Specifications for edging		
Size correction	The lens is edged <b>0.1 mm</b> smaller (especially for metal frames!)	<input checked="" type="checkbox"/>
Edge thickness	Minimum glass edge thickness of <b>1 mm</b> has been maintained	<input checked="" type="checkbox"/>
Edge finish	The lens edge is <b>not</b> polished	<input checked="" type="checkbox"/>

### 4. Send in your lenses: Done!

Everything OK? Great, then you can now send the lenses, along with the order form and, if applicable, the new customer form, to:

Shape Engineering GmbH  
 c/o shape.line  
 Gottfried Hagen Straße 60-62  
 51105 Cologne  
 Germany